

MSA PFLs Twin Connection

Technical Brief FP-PC032



The MSA Workman and Latchways Mini and standard PFLs may be used in the twin configuration either by purchasing a twin configuration complete or by joining two individual units, of the same type, via the MSA Latchways TwinLink connector – PN 63900-04 or carabiner – PN 10147792.

Please refer to the instructions provided with each unit for the preferred connection procedure to the full body harness.

The table below provides a summary of the various carabiners permitted or not permitted with each type of unit.

Carabiner	Description	Material	Twin Workmans	Twin Latchways
10089205	Dual Action Equal D	Steel	Yes	No
10147792	Triple Action Equal D	Steel	Yes	Yes
10089207	Dual Action Unequal D	Steel	No	No
63900-04	Dark Grey Gate - Triple Action TwinLink	Aluminum	Yes	Yes
	Silver Gate – Dual Action TwinLink			



Note that the TwinLink connector has been manufactured with both a dual action and triple action gate at various times due to supply availability. The triple action version has a dark grey gate while the dual action has a silver gate. Both are acceptable for use in conjunction with the TwinLink clip.

Finally, provided the proper carabiner is used as described above, it is also acceptable to attach both units via a single carabiner directly to the dorsal d-ring of the user's harness.