

# Tegaderm™ Brand

Full Line of I.V. Site Dressings

## CVC/PICC


## Peripheral IV (PIV)

## Smaller Sizes

Antimicrobial CHG


### 3M™ Tegaderm™ Chlorhexidine Gluconate (CHG) IV Securement Dressing

1657



3 1/2 in. x 4 1/2 in. (8,5 cm x 11,5 cm)

1658



4 in. x 4 3/4 in. (10 cm x 12 cm)

1659



4 in. x 6 1/8 in. (10 cm x 15,5 cm)



1660



2 3/4 in. x 3 3/8 in. (7 cm x 8,5 cm)

Advanced Securement


### 3M™ Tegaderm™ I.V. Advanced Securement Dressing

1685



3 1/2 in. x 4 1/2 in. (8,5 cm x 11,5 cm)

1688



4 in. x 4 3/4 in. (10 cm x 12 cm)

1689



4 in. x 6 1/8 in. (10 cm x 15,5 cm)

1683



2 1/2 in. x 2 3/4 in. (6,5 cm x 7 cm)

9525HP



1610



2 in. x 2 1/4 in. (5 cm x 5,7 cm)


### 3M™ Tegaderm™ Diamond Pattern Film Dressing (Improved Breathability)

1679




4 in. x 4 1/2 in. (10 cm x 11,5 cm)

1686



4 in. x 4 3/4 in. (10 cm x 12 cm)



1684



2 3/8 in. x 2 3/4 in. (6 cm x 7 cm)

### 3M™ Tegaderm™ HP (Holding Power) Transparent Film Dressing Frame Style

9546HP



4 in. x 4 1/2 in. (10 cm x 11,5 cm)

9536HP



4 in. x 4 3/4 in. (10 cm x 12 cm)

9534HP



2 3/8 in. x 2 3/4 in. (6 cm x 7 cm)

Standard Dressings

### 3M™ Tegaderm™ Transparent Film Dressing Frame Style

1630



4 in. x 4 1/2 in. (10 cm x 11,5 cm)

1626W



4 in. x 4 3/4 in. (10 cm x 12 cm)

1624W



2 3/8 in. x 2 3/4 in. (6 cm x 7 cm)

1622W



1 3/4 in. x 1 3/4 in. (4,4 cm x 4,4 cm)

### 3M™ Tegaderm™ Transparent Film Roll

16002

2 in. x 11 yd. (5 cm x 10 m)

16004

4 in. x 11 yd. (10 cm x 10 m)

16006

6 in. x 11 yd. (15 cm x 10 m)

Non-sterile, waterproof protection of skin and cover dressings



Simple. Dependable. Trusted.