

3M Separation and Purification Sciences Division Data Sheet

3M[™] LifeASSURE[™] MFE Series PTFE Membrane Filter Cartridges

3M[™] LifeASSURE[™] MFE Series Filter Cartridges have been designed for high-purity chemicals used in the electronics industry. The hydrophobic PTFE membrane in an all polypropylene construction provides excellent chemical resistance and high efficiency contaminant reduction for acids, bases, solvents and photo-chemicals used in the semiconductor, video display and hard drive industries. After manufacture and assembly, cartridges are rinsed with 18 megohm-cm DI water in a clean environment under an ISO-certified quality system to provide downstream cleanliness and then double-bagged. No pre-wetting is required for solvent based chemicals.

Features & Benefits

PTFE and Polypropylene Materials of Construction

• Robust materials provide excellent resistance in aggressive chemicals and/or dynamic pressure applications

Radial Pleat Construction

- Provides a low differential pressure to minimize bubble formation
- Increased throughput and long filter life




Chart 1: 3M[™] LifeASSURE[™] MFE Series Flow Rate vs. Differential Pressure



Applications

- Acids
- Bases
- Solvents
- Photoresists
- Anti-reflective coatings
- Plating solutions
- Glass substrates
- Hard disk drives

Materials of Construction

3M[™] LifeASSURE[™] MFE Series Filter Cartridges are constructed of high efficiency hydrophobic PTFE membrane. The outer cage, inner core, end cap adapters and membrane support layers are made of polypropylene and no adhesives, binders, or surfactants are used in the manufacturing process. Filter cartridges are manufactured and double bagged in a clean environment under an ISO quality system. All MFE series cartridges are rinsed with 18 megohm-cm DI water and integrity tested.

Specifications		
Membrane Material	Hydrophobic PTFE	
Outer Cage, Inner Core, End Cap Adapters, Membrane Support Layer	Polypropylene	
Filtration Surface Area	11.0 ft.² (1.02m²)	
Outside Diameter	Nominal 2.75 in. (7cm)	
Length	10 in. (25.4cm), 20 in. (50.8cm)	
Maximum Forward Differential Pressure	80 psid @ 77°F (5.5 bar @ 25°C) 25 psid @ 176°F (1.7 bar @ 80°C)	
Maximum Operating Temperature	176°F (80°C)	
Reduction Ratings	0.1µm	

3M[™] LifeASSURE[™] MFE Series Ordering Guide

			Description		
Model Number	3M ID	Global ID	Length	Grade	End Treatments
MFE010A01BB	70-0203-5027-1	7100194334	10 in.	0.1µm	226/Spear Fluorocarbon
MFE010A02BB	70-0201-6865-7	7010338504	20 in.	0.1µm	226/Spear Fluorocarbon
MFE010A02CK	70-0201-6976-2	7100004486	20 in.	0.1µm	226/Spear PTFE Encapsulated Fluorocarbon
MFE010A02BA	70-0203-5359-8	7100242176	20 in.	0.1µm	226/Spear SLCNE
MFE010J25AB01	70-0203-5059-4	7100206449	2.5 in.	0.1µm	2.5" Capsule, 1.5" sanitary in/out, Fluorocarbon

Intended Use and Product Selection: 3M[™] LifeASSURE[™] MFE Series Filter cartridges are intended for use in industrial and high purity chemical filtration applications of aqueous fluids in accordance with the applicable product instructions and specifications. 3M LifeASSURE MFE Series Filter cartridges are also intended for use with non-aqueous fluids where materials of construction are compatible. Since there are many factors that can affect a product's use, the customer and user remain responsible for determining whether the 3M product is suitable and appropriate for the user's specific application, including user conducting an appropriate risk assessment and evaluating the 3M product in user's application.

Restrictions on Use: 3M advises against the use of these 3M products in any application other than the stated intended use(s), since other applications have not been evaluated by 3M and may result in an unsafe or unintended condition. Do not use in any manner whereby the 3M product, or any extractable or leachable from the 3M product, may become part of or remains in a medical device, drug, cosmetic supplement, infant formula; or in applications involving life-sustaining medical applications or prolonged contact with internal bodily fluids or tissues.

3M™ LifeASSURE™ MFE Series Filter cartridges products are not for use in food contact applications.

Technical Information: The technical information, guidance, and other statements contained in this document or otherwise provided by 3M are based upon records, tests, or experience that 3M believes to be reliable, but the accuracy, completeness, and representative nature of such information is not guaranteed. Such information is intended for people with knowledge and technical skills sufficient to assess and apply their own informed judgment to the information. No license under any 3M or third party intellectual property rights is granted or implied with this information.

Product Selection and Use: Many factors beyond 3Ms control and uniquely within users knowledge and control can affect the use and performance of a 3M product in a particular application. As a result, customer is solely responsible for evaluating the product and determining whether it is appropriate and suitable for customers application, including conducting a workplace hazard assessment and reviewing all applicable regulations and standards (e.g., OSHA, ANSI, etc.). Failure to properly evaluate, select, and use a 3M product and appropriate safety products, or to meet all applicable safety regulations, may result in injury, sickness, death, and/or harm to property.

Warranty, Limited Remedy, and Disclaimer: Unless a different warranty is specifically stated on the applicable 3M product packaging or product literature (in which case such warranty governs), 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE, OR ARISING OUT OF A COURSE OF DEALING, CUSTOM, OR USAGE OF TRADE. If a 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3Ms option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability: Except for the limited remedy stated above, and except to the extent prohibited by law, 3M will not be liable for any loss or damage arising from or related to the 3M product, whether direct, indirect, special, incidental, or consequential (including, but not limited to, lost profits or business opportunity), regardless of the legal or equitable theory asserted, including, but not limited to, warranty, contract, negligence, or strict liability.



Your local distributor:

3M Purification Inc.3M Separation and Purification Sciences Division400 Research ParkwayMeriden, CT 06450 USA

Phone 1-800-243-6894 1-203-237-5541 Web 3MPurification.com

3M and LifeASSURE are trademarks of 3M Company. ©2023 3M Company. All rights reserved. Please recycle. Printed in U.S.A. 70-0201-8772-3 REV 0423